

Technical Data Sheet

Hostacom HBG H02 BLACK

Polypropylene Compounds



Product Description

Hostacom HBG H02 BLACK is a 20% glass fiber reinforced PP homopolymer, with very low melt flow rate, low creep under load at elevated temperatures, excellent hot water resistance and high dimensional stability. Please contact Basell for shrinkage recommendations. This grade is delivered in BLACK color version. Dry material before processing.

Regulatory Status

For regulatory compliance information, see Hostacom HBG H02 BLACK [Product Stewardship Bulletin \(PSB\)](#) and [Safety Data Sheet \(SDS\)](#).

This grade is not intended for medical, pharmaceutical, food and drinking water applications.

Status	Commercial: Active
Availability	Europe
Application	Underhood
Market	Automotive
Processing Method	Injection Molding

Typical Properties	Nominal Value	Units	Test Method
Physical			
Melt Flow Rate, (230 °C/5.0 kg)	0.87	g/10 min	ISO 1133-1
Melt Volume Flow Rate, (230 °C/5.0 kg)	0.6	cm ³ /10 min	ISO 1133-1
Density, (23 °C)	1.04	g/cm ³	ISO 1183-1/A
Mechanical			
Tensile Modulus, (23 °C)	4500	MPa	ISO 527-1, -2
Tensile Stress at Yield, (23 °C)	65	MPa	ISO 527-1, -2
Tensile Strain at Yield, (23 °C)	4	%	ISO 527-1, -2
Impact			
Charpy Impact Strength - Notched, (23 °C)	12	kJ/m ²	ISO 179-1/1eA
Charpy Impact Strength - Unnotched, (23 °C)	45	kJ/m ²	ISO 179-1/1eU
Thermal			
Vicat Softening Temperature, (B50)	120	°C	ISO 306
Deflection Temperature Under Load, (1.80 MPa, Unannealed)	112	°C	ISO 75A-1, -2

Notes

These are typical property values not to be construed as specification limits.

Availability indicates the region where the material is produced. For importation or demand of a local equivalent grade, please contact our Sales Representatives.

LyondellBasell
Technical Data Sheet
Date: 7/25/2017

Page 1 of 3

Hostacom HBG H02 BLACK
Recipient Tracking #:
Request #: 908507

Processing Techniques

Specific recommendations for resin type and processing conditions can only be made when the end use, required properties and fabrication equipment are known.

Product Storage and Handling

- Product should be stored in dry conditions at temperatures below 50°C and protected from UV-light
- Improper storage may bring damage to the packaging and can negatively affects on the quality of this product
- Keep material completely dry for good processing

Company Information

For further information regarding the LyondellBasell company, please visit <http://www.lyb.com/>.

© LyondellBasell Industries Holdings, B.V. 2017

Disclaimer

Before using a product sold by a company of the LyondellBasell family of companies, users should make their own independent determination that the product is suitable for the intended use and can be used safely and legally.

SELLER MAKES NO WARRANTY; EXPRESS OR IMPLIED (INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY WARRANTY) OTHER THAN AS SEPARATELY AGREED TO BY THE PARTIES IN A CONTRACT.

Users should review the applicable Safety Data Sheet before handling the product.

This product(s) may not be used in the manufacture of any of the following, without prior written approval by Seller for each specific product and application:

- (i) U.S. FDA Class I or II Medical Devices; Health Canada Class I, II or III Medical Devices; European Union Class I or II Medical Devices;
- (ii) film, overwrap and/or product packaging that is considered a part or component of one of the aforementioned medical devices;
- (iii) packaging in direct contact with a pharmaceutical active ingredient and/or dosage form that is intended for inhalation, injection, intravenous, nasal, ophthalmic (eye), digestive, or topical (skin) administration;
- (iv) tobacco related products and applications, electronic cigarettes and similar devices.
- (v) safety components in automotive applications, for example: air bags, air bag unit housings and covers, seat belt mechanisms, brake systems, pedals and pedal supports, steering systems.

The product(s) may not be used in:

- (i) U.S. FDA Class III Medical Devices; Health Canada Class IV Medical Devices; European Class III Medical Devices;
- (ii) applications involving permanent implantation into the body;
- (iii) life-sustaining medical applications.

All references to U.S. FDA, Health Canada, and European Union regulations include another country's equivalent regulatory classification.

In addition to the above, LyondellBasell may further prohibit or restrict the use of its products in certain applications. For further information, please contact a LyondellBasell representative.

Trademarks

Adflex, Adstif, Adsyl, Akoafloor, Akoalit, Alastian, Alathon, Alkylate, Amazing Chemistry, Aquamarine, Aquathene, Avant, Catalloy, Clyrell, CRP, Crystex, Dexflex, Duopac, Duoprime, Explore & Experiment, Filmex, Flexathene, Fueling the power to win, Glacido, Hifax, Hiflex, Histif, Hostacom, Hostalen, Hyperzone, Ideal, Indure, Integrate, Koattro, LIPP, Lucalen, Luflexen, Lupolen, Luposim, Lupostress, Lupotech, Metocene, Microthene, Moplen, MPDIOL, Nerolex, Nexprene, Petrothene, Plexar, Polymeg, Pristene, Prodflex, Pro-fax, Punctilious, Purell, Refax, SAA100, SAA101, Sequel, Softell, Spherilene, Spheripol, Spherizone, Starflex, Stretchene, Superflex, TBAC, Tebol, T-Hydro, Toppyl, Trans4m, Tufflo, Ultrathene, Vacido and Valtec are trademarks owned and/or used by the LyondellBasell family of companies.

Adsyl, Akoafloor, Akoalit, Alastian, Alathon, Aquamarine, Avant, CRP, Crystex, Dexflex, Duopac, Duoprime, Explore & Experiment, Filmex, Flexathene, Hifax, Hostacom, Hostalen, Ideal, Integrate, Koattro, Lucalen, Lupolen, Metocene, Microthene, Moplen, MPDIOL, Nexprene, Petrothene, Plexar, Polymeg, Pristene, Pro-fax, Punctilious, Purell, Sequel, Softell, Spheripol, Spherizone, Starflex, Tebol, T-Hydro, Toppyl, Tufflo and Ultrathene are registered in the U.S. Patent and Trademark Office.