



Hostalen CRP 100 blue

Polyethylene, High Density

Product Description

Hostalen CRP 100 blue is a high density polyethylene (HDPE), blue coloured similar RAL 5005 with high melt viscosity for extrusion, injection and compression moulding. The product is classified as PE 100 and provides excellent stress crack resistance properties (ESCR) combined with very good long term hydrostatic strength. It is not intended for medical and pharmaceutical applications.

Product Characteristics

Status	Commercial: Active
Test Method used	ISO
Availability	Asia-Pacific, Australia/NZ, Africa-Middle East
Processing Methods	Extrusion Pipe Sheet and Semi Finished Products
Typical Customer Applications	Drinking Water Pipe

Typical Properties	Method	Value Unit
Physical		
Density	ISO 1183	0.95 g/cm ³
Melt flow rate (MFR)	ISO 1133	
(190°C/21.6kg)		6.4 g/10 min
(190°C/5.0kg)		0.23 g/10 min
Mechanical		
Tensile Modulus (23 °C, v = 1 mm/min, Secant)	ISO 527-1, -2	850 MPa
Tensile Stress at Yield (23 °C, v = 50 mm/min)	ISO 527-1, -2	23 MPa
Tensile Strain at Yield (23 °C, v = 50 mm/min)	ISO 527-1, -2	8 %
Tensile Creep Modulus 1h	ISO 899-1	800 [2.0] MPa
<i>Note: [Test stress in MPa]</i>		
Tensile Creep Modulus 1000h	ISO 899-1	350 [2.0] MPa
<i>Note: [Test stress in MPa]</i>		
MRS classification	ISO/TR 9080	10 MPa
Flexural stress at 3,5% deflection	ISO 178	20 MPa
FNCT (4.0 MPa, 2% Arkopal N 100, 80°C)	ISO 16770	≥ 1000 h
Flexural creep modulus	DIN 19537-2	
(4 point loading method, 1 min-value)		1100 MPa
(4 point loading method, 24 h-value)		560 MPa
(4 point loading method, 2000 h-value)		330 MPa
Impact		
Charpy notched impact strength	ISO 179	
(23 °C)		29 kJ/m ²
(-30 °C)		15 kJ/m ²
Hardness		
Shore hardness (Shore D (3 sec))	ISO 868	62
Thermal		
Vicat softening temperature (VST/B/50 K/h (50 N))	ISO 306	74 °C
Oxidation induction time (OIT) (210°C)	ISO 11357-6 / EN 728	30 min

Additional Properties

Processing:
Recommended melt temperatures: 190-220 °C.
Recommended injection moulding temperatures: 200-280 °C.

Notes

Typical properties; not to be construed as specifications.

Further Information

Conveying:

Conveying equipment should be designed to prevent production and accumulation of fines and dust particles that may be contained to a small extent in polymer materials. These particles can under certain conditions pose an explosion hazard. We recommend the conveying system used is equipped with adequate filters, is operated and maintained so that no leak develops and adequate electrical grounding exists at all times.

Health and Safety:

Special requirements apply to certain applications such as food contact end-use and direct medical use. For specific information on regulatory compliance contact your local representative.

Workers should be protected from the possibility of skin or eye contact with molten polymer. Safety glasses are suggested as a minimum precaution to prevent mechanical or thermal injury to the eyes.

Molten polymer may be degraded if it is exposed to air during any of the processing and off-line operations. The products of degradation have an unpleasant odour. In higher concentrations they may cause irritation of the mucus membranes. Fabrication areas should be ventilated to carry away fumes or vapours. Legislation on the control of emissions and pollution prevention must be observed. If the principles of sound manufacturing practice are adhered to and the place of work is well ventilated, no health hazards in processing the material have been reported.

The material will burn when supplied with excess heat and oxygen. It should be handled and stored away from contact with direct flames and/or ignition sources. In burning the material generates considerable heat and may generate dense black smoke. Minor fires can be extinguished by water, developed fires should be extinguished by heavy foams forming an aqueous or polymeric film. For further information about safety in handling and processing please refer to the Material Safety Data Sheet (MSDS).

Storage:

The material is packed in 25 kg bags or in bulk containers protecting it from contamination. Storage times of natural materials longer than 6 months may have a negative influence on the quality of the final product (for example the brightness). It is generally recommended to convert all materials latest within 6 months from the date of delivery.

The material is subjected to degradation by ultra-violet radiation or by high storage temperatures. Therefore the material must be protected from direct sunlight, temperatures above 40°C and high atmospheric humidity during storage.

Further unfavourable storage conditions are large fluctuations in ambient temperature and high atmospheric humidity. These conditions may lead to moisture condensing inside the packaging. Under these circumstances, it is recommended to dry the material before use. Unfavourable storage conditions may also intensify the material's slight characteristic odour.

Due the hygroscopic character of the carbon black pigments, black coloured materials may pick up moisture even under appropriate storage conditions. If this is the case it is recommended to dry the material before processing. After a storage period of more than 3 months drying of such material is recommended as standard practice.

© LyondellBasell Industries Holdings, B.V. 2012

LyondellBasell markets this product through the following entities:

- l Equistar Chemicals, LP
- l Basell Sales & Marketing Company B.V.
- l Basell Asia Pacific Limited
- l Basell International Trading FZE
- l LyondellBasell Australia Pty Ltd

For the contact details of the LyondellBasell company selling this product in your country, please visit <http://www.lyondellbasell.com/>.

Before using a product sold by a company of the LyondellBasell family of companies, users should make their own independent determination that the product is suitable for the intended use and can be used safely and legally. SELLER MAKES NO WARRANTY; EXPRESS OR IMPLIED (INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY WARRANTY) OTHER THAN AS SEPARATELY AGREED TO BY THE PARTIES IN A CONTRACT.

This product(s) may not be used in:

(i) any U.S. FDA Class I, Health Canada Class I, and/or European Union Class I medical devices, without prior notification to Seller for each specific product and application; or
(ii) the manufacture of any of the following, without prior written approval by Seller for each specific product and application: U.S. FDA Class II medical devices; Health Canada Class II or III medical devices; European Union Class II medical devices; or any equivalent U.S. FDA, Health Canada, or European Union regulations pertaining to medical devices; packaging in direct contact with a pharmaceutical active ingredient and/or dosage form; and tobacco-related products and applications. This product(s) may not be used in the manufacture of any of the following applications: U.S. FDA Class III medical devices; Health Canada Class IV medical devices; European Class III medical devices; applications involving permanent implantation into the body; life-sustaining medical applications; and lead, asbestos or MTBE related applications. All references to the U.S. FDA, Health Canada and European Union regulations include another country's equivalent regulatory classification.

Users should review the applicable Material Safety Data Sheet before handling the product.

Addhere, Adflex, Adstif, Adsyl, Akoafloor, Akoalit, Alathon, Alkylate, Amazing Chemistry, Aquamarine, Aquathene, Arconate, Arcopure, Arcosolv, Arctic Plus, Arctic Shield, Avant, Catalloy, Clyrell, CRP, Crystex, Dexflex, Duopac, Duoprime, Explore & Experiment, Filmex, Flexathene, Glacido, Hifax, Histif, Hostacom, Hostalen, Ideal, Integrate, Koattro, LIPP, Lucalen, Luflexen, Lupolen, Lupolex, Luposim, Lupostress, Lupotech, Metocene, Microthene, Moplen, MPDIOL, Nerolex, Nexprene, Petrothene, Plexar, Polymeg, Pristene, Proflex, Pro-Fax, Punctilious, Purell, SAA100, SAA101, Sequel, Softell, Spherilene, Spheripol, Spherizone, Starflex, Stretchene, Superflex, TBAC, Tebol, T-Hydro, Toppyl, Trans4m, Tufflo, Ultrathene, Vacido and Valtec are trademarks owned or used by the LyondellBasell family of companies.

Adsyl, Akoafloor, Akoalit, Alathon, Aquamarine, Arconate, Arcopure, Arcosolv, Arctic Plus, Arctic Shield, Avant, CRP, Crystex, Dexflex, Duopac, Duoprime, Explore & Experiment, Filmex, Flexathene, Hifax, Hostacom, Hostalen, Ideal, Integrate, Koattro, Lucalen, Lupolen, Microthene, Moplen, MPDIOL, Nexprene, Petrothene, Plexar, Polymeg, Pristene, Pro-Fax, Punctilious, Purell, Sequel, Softell, Spheripol, Spherizone, Starflex, Tebol, T-Hydro, Toppyl, Tufflo and Ultrathene are registered in the U.S. Patent and Trademark Office.

Release Date: 23 Aug 2013