

Technical Data Sheet

Hostalen GD 7255 LS

High Density Polyethylene



Product Description

Hostalen GD 7255 LS is a high density polyethylene resin stabilized to prevent UV degradation. It's used in general injection molding applications such as pallets and dust bin bodies. *Hostalen* GD 7255 LS is available in pellet form, and exhibits high ESCR, good impact resistance, flowability and low warpage.

Hostalen GD 7255 LS is not intended for use in medical and pharmaceutical applications.

Regulatory Status

For regulatory compliance information, see *Hostalen* GD 7255 LS [Product Stewardship Bulletin \(PSB\)](#) and [Safety Data Sheet \(SDS\)](#).

Status	Commercial: Active
Availability	Africa-Middle East; Asia-Pacific; Australia and New Zealand; Europe; South & Central America
Application	Crates; Housewares; Industrial; Panels & Profiles; Sports, Leisure & Toys
Market	Consumer Products; Rigid Packaging
Processing Method	Injection Molding
Attribute	Antioxidant; Good Flow; Good Processability; High Density; High Impact Resistance; High Rigidity; Low Warpage; UV Resistant

Typical Properties	Nominal Value	Units	Test Method
Physical			
Melt Flow Rate			
(190 °C/2.16 kg)	4.0	g/10 min	ISO 1133-1
(190 °C/5.0 kg)	11.0	g/10 min	ISO 1133-1
Density	0.955	g/cm ³	ISO 1183-1
Mechanical			
Tensile Modulus	1200	MPa	ISO 527-1, -2
Tensile Stress at Yield	27	MPa	ISO 527-1, -2
Tensile Strain at Yield	8	%	ISO 527-1, -2
FNCT, (6.0 MPa, 2% Arkopal N100, 50 °C)	4.5	hr	ISO 16770
Impact			
Charpy Impact Strength - Notched			
(23 °C, Type 1, Edgewise, Notch A)	4.0	kJ/m ²	ISO 179
(-30 °C, Type 1, Edgewise, Notch A)	4.5	kJ/m ²	ISO 179
Hardness			
Shore Hardness, (Shore D)	60		ISO 868
Ball Indentation Hardness, (H 132/30)	52	MPa	ISO 2039-1
Thermal			
Vicat Softening Temperature, (B50)	73	°C	ISO 306

LyondellBasell
Technical Data Sheet
Date: 7/25/2017

Page 1 of 5

Hostalen GD 7255 LS
Recipient Tracking #:
Request #: 907906

Processing Parameters

Melt Temperature	180 - 250 °C
------------------	--------------

Notes

These are typical property values not to be construed as specification limits.

Processing Techniques

Users should determine the conditions necessary to obtain optimum product properties and suitability of the product for the intended application.

In cases where higher temperatures are required, please contact your appropriate technical contact for support.

Further Information**Health and Safety:**

The resin is manufactured to the highest standards, but special requirements apply to certain applications such as food end-use contact and direct medical use. For specific information on regulatory compliance contact your local representative.

Workers should be protected from the possibility of skin or eye contact with molten polymer. Safety glasses are suggested as a minimal precaution to prevent mechanical or thermal injury to the eyes.

Molten polymer may be degraded if it is exposed to air during any of the processing and off-line operations. The products of degradation may have an unpleasant odor. In higher concentrations they may cause irritation of the mucus membranes. Fabrication areas should be ventilated to carry away fumes or vapours. Legislation on the control of emissions and pollution prevention should be observed.

The resin will burn when supplied with excess heat and oxygen. It should be handled and stored away from contact with direct flames and/or ignition sources. While burning, the resin contributes high heat and may generate a dense black smoke.

Recycled resins may have previously been used as packaging for, or may have otherwise been in contact with, hazardous goods. Converters are responsible for taking all necessary precautions to ensure that recycled resins are safe for continued use.

For further information about safety in handling and processing please refer to the Safety Data Sheet.

Conveying:

Conveying equipment should be designed to prevent production and accumulation of fines and dust particles that are contained in polymer resins. These particles can under certain conditions pose an explosion hazard. Conveying systems should be grounded, equipped with adequate filters and regularly inspected for leaks.

Storage:

The resin is packed in 25 kg bags, octabins or bulk containers protecting it from contamination. If it is stored under certain conditions, i. e. if there are large fluctuations in ambient temperature and the atmospheric humidity is high, moisture may condense inside the packaging. Under these circumstances, it is recommended to dry the resin before use. Unfavorable storage conditions may also intensify the resin's slight characteristic odor.

Resin should be protected from direct sunlight, temperatures above 40°C and high atmospheric humidity during storage. Higher storage temperatures may reduce the storage time.

The information submitted is based on our current knowledge and experience. In view of the many factors that may affect processing and application, these data do not relieve processors of the responsibility of carrying out their own tests and experiments; neither do they imply any legally binding assurance of certain properties or of suitability for a specific purpose. This information does not remove the obligation of the customer to inspect the material on arrival and notify us of any faults immediately. It is the responsibility of those to whom we supply our products to ensure that any proprietary rights and existing laws and legislation are observed.

Company Information

For further information regarding the LyondellBasell company, please visit <http://www.lyb.com/>.

© LyondellBasell Industries Holdings, B.V. 2017

Disclaimer

Before using a product sold by a company of the LyondellBasell family of companies, users should make their own independent determination that the product is suitable for the intended use and can be used safely and legally.

SELLER MAKES NO WARRANTY; EXPRESS OR IMPLIED (INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY WARRANTY) OTHER THAN AS SEPARATELY AGREED TO BY THE PARTIES IN A CONTRACT.

Users should review the applicable Safety Data Sheet before handling the product.

This product(s) may not be used in the manufacture of any of the following, without prior written approval by Seller for each specific product and application:

- (i) U.S. FDA Class I or II Medical Devices; Health Canada Class I, II or III Medical Devices; European Union Class I or II Medical Devices;
- (ii) film, overwrap and/or product packaging that is considered a part or component of one of the aforementioned medical devices;
- (iii) packaging in direct contact with a pharmaceutical active ingredient and/or dosage form that is intended for inhalation, injection, intravenous, nasal, ophthalmic (eye), digestive, or topical (skin) administration;
- (iv) tobacco related products and applications, electronic cigarettes and similar devices.
- (v) safety components in automotive applications, for example: air bags, air bag unit housings and covers, seat belt mechanisms, brake systems, pedals and pedal supports, steering systems.

The product(s) may not be used in:

- (i) U.S. FDA Class III Medical Devices; Health Canada Class IV Medical Devices; European Class III Medical Devices;
- (ii) applications involving permanent implantation into the body;
- (iii) life-sustaining medical applications.

All references to U.S. FDA, Health Canada, and European Union regulations include another country's equivalent regulatory classification.

In addition to the above, LyondellBasell may further prohibit or restrict the use of its products in certain applications. For further information, please contact a LyondellBasell representative.

Trademarks

Adflex, Adstif, Adsyl, Akoafloor, Akoalit, Alastian, Alathon, Alkylate, Amazing Chemistry, Aquamarine, Aquathene, Avant, Catalloy, Clyrell, CRP, Crystex, Dexflex, Duopac, Duoprime, Explore & Experiment, Filmex, Flexathene, Fueling the power to win, Glacido, Hifax, Hiflex, Histif, Hostacom, Hostalen, Hyperzone, Ideal, Indure, Integrate, Koattro, LIPP, Lucalen, Luflexen, Lupolen, Luposim, Lupostress, Lupotech, Metocene, Microthene, Moplen, MPDIOL, Nerolex, Nexprene, Petrothene, Plexar, Polymeg, Pristene, Prodflex, Pro-fax, Punctilious, Purell, Refax, SAA100, SAA101, Sequel, Softell, Spherilene, Spheripol, Spherizone, Starflex, Stretchene, Superflex, TBAC, Tebol, T-Hydro, Toppyl, Trans4m, Tufflo, Ultrathene, Vacido and Valtec are trademarks owned and/or used by the LyondellBasell family of companies.

Adsyl, Akoafloor, Akoalit, Alastian, Alathon, Aquamarine, Avant, CRP, Crystex, Dexflex, Duopac, Duoprime, Explore & Experiment, Filmex, Flexathene, Hifax, Hostacom, Hostalen, Ideal, Integrate, Koattro, Lucalen, Lupolen, Metocene, Microthene, Moplen, MPDIOL, Nexprene, Petrothene, Plexar, Polymeg, Pristene, Pro-fax, Punctilious, Purell, Sequel, Softell, Spheripol, Spherizone, Starflex, Tebol, T-Hydro, Toppyl, Tufflo and Ultrathene are registered in the U.S. Patent and Trademark Office.

