

Technical Data Sheet

Petrothene GA502119

Linear Low Density Polyethylene



Product Description

The *Petrothene* GA502 series of resins are pelletized linear low density polyethylenes for applications requiring excellent drawdown and toughness. These pelletized products offer excellent additive homogeneity, require no transfer equipment modification and facilitate clean and safe storage and handling. They can be used in either blown or cast film extrusion. GA502119 is formulated without TNPP.

Regulatory Status

For regulatory compliance information, see *Petrothene* GA502119 [Product Stewardship Bulletin \(PSB\)](#) and [Safety Data Sheet \(SDS\)](#).

Status	Commercial: Active
Availability	North America
Application	Bags & Pouches; Can Liners; Colour Concentrates; Film Wrap; Food Packaging Film; Lamination Film; Liner Film; Stretch Wrap Film
Market	Flexible Packaging
Processing Method	Blown Film; Cast Film; Compounding

Typical Properties	Nominal Value	English Units	Nominal Value	SI Units	Test Method
Physical					
Melt Flow Rate, (190 °C/2.16 kg)	2.0	g/10 min	2.0	g/10 min	ASTM D1238
Base Resin Density, (23 °C)	0.918	g/cm ³	0.918	g/cm ³	ASTM D1505
Product Density, (23 °C)	0.918	g/cm ³	0.918	g/cm ³	ASTM D1505
Film					
Dart Drop Impact Strength, F50	120	g	120	g	ASTM D1709
Tensile Strength at Break					
MD	4900	psi	33.8	MPa	ASTM D882
TD	3600	psi	24.8	MPa	ASTM D882
Tensile Elongation at Break					
MD	750	%	750	%	ASTM D882
TD	800	%	800	%	ASTM D882
1% Secant Modulus					
MD	32000	psi	221	MPa	ASTM D882
TD	36000	psi	248	MPa	ASTM D882
Elmendorf Tear Strength					
MD	170	g	170	g	ASTM D1922
TD	400	g	400	g	ASTM D1922
Additive					
Slip	None		None		LYB Method
Antiblock	None		None		LYB Method

Product	Product Density(g/cm ³)	Slip(ppm)	Antiblock (ppm)
GA502022	0.923	1350	7000
GA502023	0.922	900	5500
GA502024	0.918	None	None
GA502119	0.918	None	None

Notes

Film sample used for testing was 1.5 mil gauge, 2.1:1 BUR.

These are typical property values not to be construed as specification limits.

Processing Techniques

Specific recommendations for resin type and processing conditions can only be made when the end use, required properties and fabrication equipment are known.

Company Information

For further information regarding the LyondellBasell company, please visit <http://www.lyb.com/>.

© LyondellBasell Industries Holdings, B.V. 2017

Disclaimer

Before using a product sold by a company of the LyondellBasell family of companies, users should make their own independent determination that the product is suitable for the intended use and can be used safely and legally.

SELLER MAKES NO WARRANTY; EXPRESS OR IMPLIED (INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY WARRANTY) OTHER THAN AS SEPARATELY AGREED TO BY THE PARTIES IN A CONTRACT.

Users should review the applicable Safety Data Sheet before handling the product.

This product(s) may not be used in the manufacture of any of the following, without prior written approval by Seller for each specific product and application:

- (i) U.S. FDA Class I or II Medical Devices; Health Canada Class I, II or III Medical Devices; European Union Class I or II Medical Devices;
- (ii) film, overwrap and/or product packaging that is considered a part or component of one of the aforementioned medical devices;
- (iii) packaging in direct contact with a pharmaceutical active ingredient and/or dosage form that is intended for inhalation, injection, intravenous, nasal, ophthalmic (eye), digestive, or topical (skin) administration;
- (iv) tobacco related products and applications, electronic cigarettes and similar devices.
- (v) safety components in automotive applications, for example: air bags, air bag unit housings and covers, seat belt mechanisms, brake systems, pedals and pedal supports, steering systems.

The product(s) may not be used in:

- (i) U.S. FDA Class III Medical Devices; Health Canada Class IV Medical Devices; European Class III Medical Devices;
- (ii) applications involving permanent implantation into the body;
- (iii) life-sustaining medical applications.

All references to U.S. FDA, Health Canada, and European Union regulations include another country's equivalent regulatory classification.

In addition to the above, LyondellBasell may further prohibit or restrict the use of its products in certain applications. For further information, please contact a LyondellBasell representative.

Trademarks

Adflex, Adstif, Adsyl, Akoafloor, Akoalit, Alastian, Alathon, Alkylate, Amazing Chemistry, Aquamarine, Aquathene, Avant, Catalloy, Clyrell, CRP, Crystex, Dexflex, Duopac, Duoprime, Explore & Experiment, Filmex, Flexathene, Fueling the power to win, Glacido, Hifax, Hiflex, Histif, Hostacom, Hostalen, Hyperzone, Ideal, Indure, Integrate, Koattro, LIPP, Lucalen, Luflexen, Lupolen, Luposim, Lupostress, Lupotech, Metocene, Microthene, Moplen, MPDIOL, Nerolex, Nexprene, Petrothene, Plexar, Polymeg, Pristene, Prodflex, Pro-fax, Punctilious, Purell, Refax, SAA100, SAA101, Sequel, Softell, Spherilene, Spheripol, Spherizone, Starflex, Stretchene, Superflex, TBAC, Tebol, T-Hydro, Toppyl, Trans4m, Tufflo, Ultrathene, Vacido and Valtec are trademarks owned and/or used by the LyondellBasell family of companies.

Adsyl, Akoafloor, Akoalit, Alastian, Alathon, Aquamarine, Avant, CRP, Crystex, Dexflex, Duopac, Duoprime, Explore & Experiment, Filmex, Flexathene, Hifax, Hostacom, Hostalen, Ideal, Integrate, Koattro, Lucalen, Lupolen, Metocene, Microthene, Moplen, MPDIOL, Nexprene, Petrothene, Plexar, Polymeg, Pristene, Pro-fax, Punctilious, Purell, Sequel, Softell, Spheripol, Spherizone, Starflex, Tebol, T-Hydro, Toppyl, Tufflo and Ultrathene are registered in the U.S. Patent and Trademark Office.

