

Technical Data Sheet

Petrothene GA601030

Linear Low Density Polyethylene



Product Description

The *Petrothene* GA601 series resins are pelletized linear low density polyethylenes selected by customers for applications that require maximum strength and toughness. These products offer excellent additive homogeneity, require no transfer equipment modification, and facilitate clean and safe handling. Typical applications include heavy duty shipping sacks, trash can liners, commercial and industrial packaging, as well as food and consumer packaging. The GA601 series resins offer enhanced film strength, drawdown, toughness and heat seal strength. In addition, these resins have excellent low temperature resistance for applications such as stretch film and frozen food packaging. The GA601 series resins can be purchased without additives or fully formulated with slip and antiblock.

Regulatory Status

For regulatory compliance information, see *Petrothene* GA601030 [Product Stewardship Bulletin \(PSB\)](#) and [Safety Data Sheet \(SDS\)](#).

Status	Commercial: Active
Availability	North America
Application	Agriculture Film; Bags & Pouches; Can Liners; Film Wrap; Food Packaging Film; Heavy Duty Packaging; Lamination Film; Liner Film; Retail Carryout Bags; Shrink Film
Market	Flexible Packaging; Rigid Packaging
Processing Method	Blown Film; Sheet and Profile Extrusion

Typical Properties	Nominal Value	English Units	Nominal Value	SI Units	Test Method
Physical					
Melt Flow Rate, (190 °C/2.16 kg)	1.0	g/10 min	1.0	g/10 min	ASTM D1238
Base Resin Density, (23 °C)	0.918	g/cm³	0.918	g/cm³	ASTM D1505
Product Density, (23 °C)	0.918	g/cm³	0.918	g/cm³	ASTM D1505
Film					
Dart Drop Impact Strength, F50	190	g	190	g	ASTM D1709
Tensile Strength at Break					
MD	8100	psi	55.8	MPa	ASTM D882
TD	6100	psi	42.1	MPa	ASTM D882
Tensile Elongation at Break					
MD	580	%	580	%	ASTM D882
TD	700	%	700	%	ASTM D882
1% Secant Modulus					
MD	29000	psi	200	MPa	ASTM D882
TD	32500	psi	224	MPa	ASTM D882
Elmendorf Tear Strength					
MD	325	g	325	g	ASTM D1922
TD	650	g	650	g	ASTM D1922

Thermal			
Vicat Softening Point	221 °F	105 °C	ASTM D1525
Additive			
Slip	None	None	LYB Method
Antiblock	None	None	LYB Method

Product	Product		Antiblock (ppm)
	Density(g/cm³)	Slip(ppm)	
GA601030	0.918	None	None
GA601031	0.922	None	6500
GA601032	0.922	1350	6500
GA601033	0.922	900	6500

Notes

Film sample used for testing was 1.0 mil gauge, 2.5:1 BUR.

These are typical property values not to be construed as specification limits.

Processing Techniques

Recommended processing conditions for this product are a melt temperature of 400 - 450 °F and a 1.5 to 3.0:1 blow-up ratio.

Using proper techniques, these products can readily be drawn below 0.90 mils at optimum production rates.

Specific recommendations for resin type and processing conditions can only be made when the end use, required properties and fabrication equipment are known.

Company Information

For further information regarding the LyondellBasell company, please visit <http://www.lyb.com/>.

© LyondellBasell Industries Holdings, B.V. 2017

Disclaimer

Before using a product sold by a company of the LyondellBasell family of companies, users should make their own independent determination that the product is suitable for the intended use and can be used safely and legally.

SELLER MAKES NO WARRANTY; EXPRESS OR IMPLIED (INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY WARRANTY) OTHER THAN AS SEPARATELY AGREED TO BY THE PARTIES IN A CONTRACT.

Users should review the applicable Safety Data Sheet before handling the product.

This product(s) may not be used in the manufacture of any of the following, without prior written approval by Seller for each specific product and application:

- (i) U.S. FDA Class I or II Medical Devices; Health Canada Class I, II or III Medical Devices; European Union Class I or II Medical Devices;
- (ii) film, overwrap and/or product packaging that is considered a part or component of one of the aforementioned medical devices;
- (iii) packaging in direct contact with a pharmaceutical active ingredient and/or dosage form that is intended for inhalation, injection, intravenous, nasal, ophthalmic (eye), digestive, or topical (skin) administration;
- (iv) tobacco related products and applications, electronic cigarettes and similar devices.
- (v) safety components in automotive applications, for example: air bags, air bag unit housings and covers, seat belt mechanisms, brake systems, pedals and pedal supports, steering systems.

The product(s) may not be used in:

- (i) U.S. FDA Class III Medical Devices; Health Canada Class IV Medical Devices; European Class III Medical Devices;
- (ii) applications involving permanent implantation into the body;
- (iii) life-sustaining medical applications.

All references to U.S. FDA, Health Canada, and European Union regulations include another country's equivalent regulatory classification.

In addition to the above, LyondellBasell may further prohibit or restrict the use of its products in certain applications. For further information, please contact a LyondellBasell representative.

Trademarks

Adflex, Adstif, Adsyl, Akoafloor, Akoalit, Alastian, Alathon, Alkylate, Amazing Chemistry, Aquamarine, Aquathene, Avant, Catalloy, Clyrell, CRP, Crystex, Dexflex, Duopac, Duoprime, Explore & Experiment, Filmex, Flexathene, Fueling the power to win, Glacido, Hifax, Hiflex, Histif, Hostacom, Hostalen, Hyperzone, Ideal, Indure, Integrate, Koattro, LIPP, Lucalen, Luflexen, Lupolen, Luposim, Lupostress, Lupotech, Metocene, Microthene, Moplen, MPDIOL, Nerolex, Nexprene, Petrothene, Plexar, Polymeg, Pristene, Prodflex, Pro-fax, Punctilious, Purell, Refax, SAA100, SAA101, Sequel, Softell, Spherilene, Spheripol, Spherizone, Starflex, Stretchene, Superflex, TBAC, Tebol, T-Hydro, Toppyl, Trans4m, Tufflo, Ultrathene, Vacido and Valtec are trademarks owned and/or used by the LyondellBasell family of companies.

Adsyl, Akoafloor, Akoalit, Alastian, Alathon, Aquamarine, Avant, CRP, Crystex, Dexflex, Duopac, Duoprime, Explore & Experiment, Filmex, Flexathene, Hifax, Hostacom, Hostalen, Ideal, Integrate, Koattro, Lucalen, Lupolen, Metocene, Microthene, Moplen, MPDIOL, Nexprene, Petrothene, Plexar, Polymeg, Pristene, Pro-fax, Punctilious, Purell, Sequel, Softell, Spheripol, Spherizone, Starflex, Tebol, T-Hydro, Toppyl, Tufflo and Ultrathene are registered in the U.S. Patent and Trademark Office.

