

Technical Data Sheet

Petrothene GA808093

W&C Polyolefin Compound



Product Description

Petrothene GA808093 is a broad molecular weight, linear low density polyethylene resin selected by customers for use as wire and cable insulation. An antioxidant package has been added to ensure thermal stability during processing. The resin also contains a metal deactivator to prevent degradation from copper while the cable is in service.

Petrothene GA808093 meets the requirements of the following: ASTM D 1248, Type I, Class A, Category 4, Grade E5; Federal LP390C, Type II, Class L, Category 4, Grade 4.

Regulatory Status

For regulatory compliance information, see *Petrothene* GA808093 [Product Stewardship Bulletin \(PSB\)](#) and [Safety Data Sheet \(SDS\)](#).

Status	Commercial: Active
Availability	North America
Application	Wire & Cable
Market	Wire & Cable
Processing Method	Wire & Cable

Typical Properties	Nominal Value	English Units	Nominal Value	SI Units	Test Method
Physical					
Melt Flow Rate, (190 °C/2.16 kg)	0.70	g/10 min	0.70	g/10 min	ASTM D1238
Density, (23 °C)	0.920	g/cm ³	0.920	g/cm ³	ASTM D1505
Mechanical					
Flexural Modulus, (1% Secant)	50000	psi	345	MPa	ASTM D790
Tensile Stress at Break	2200	psi	15.2	MPa	ASTM D638
Tensile Stress at Yield	1700	psi	12.0	MPa	ASTM D638
Tensile Elongation at Break	650	%	650	%	ASTM D638
Environmental Stress Crack Resistance, F ₂₀ (10% Igepal®, Cond A)	>1000	hr	>1000	hr	ASTM D1693
Hardness					
Shore Hardness, (Shore D)	57		57		ASTM D2240
Thermal					
Low Temperature Brittleness, F ₅₀	<-105	°F	<-76	°C	ASTM D746
Electrical					
Dielectric Constant, 1 MHz	2.29		2.29		ASTM D150
Dissipation Factor, 1 MHz	0.00010		0.00010		ASTM D150

Notes

LyondellBasell
Technical Data Sheet
Date: 7/25/2017

Petrothene GA808093
Recipient Tracking #:
Request #: 907619

Igepal® is a registered trademark of Rhodia.

These are typical property values not to be construed as specification limits.

Processing Techniques

Specific recommendations for resin type and processing conditions can only be made when the end use, required properties and fabrication equipment are known.

General Extrusion Conditions

Petrothene GA808093, like other thermoplastic polyolefin resins, can be extruded using a conventional extruder. Below are suggested extrusion conditions for *Petrothene* GA808093. These conditions are intended as general guidelines only, and are not optimum values, since manufacturing variables such as extruder type and size have an effect on processing of thermoplastic resins.

<u>Extruder Zone</u>	<u>Temperature Range</u>	<u>Extruder Zone</u>	<u>Temperature Range</u>
Feed	310 - 325 °F (154 - 163 °C)	Zone 4-X	400 - 425 °F (204 - 218 °C)
Zone 2	350 - 380 °F (177 - 193 °C)	Adapter	400 - 425 °F (204 - 218 °C)
Zone 3	380 - 410 °F (193 - 210 °C)	Die	400 - 425 °F (204 - 218 °C)

Company Information

For further information regarding the LyondellBasell company, please visit <http://www.lyb.com/>.

© LyondellBasell Industries Holdings, B.V. 2017

Disclaimer

Before using a product sold by a company of the LyondellBasell family of companies, users should make their own independent determination that the product is suitable for the intended use and can be used safely and legally.

SELLER MAKES NO WARRANTY; EXPRESS OR IMPLIED (INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY WARRANTY) OTHER THAN AS SEPARATELY AGREED TO BY THE PARTIES IN A CONTRACT.

Users should review the applicable Safety Data Sheet before handling the product.

This product(s) may not be used in the manufacture of any of the following, without prior written approval by Seller for each specific product and application:

- (i) U.S. FDA Class I or II Medical Devices; Health Canada Class I, II or III Medical Devices; European Union Class I or II Medical Devices;
- (ii) film, overwrap and/or product packaging that is considered a part or component of one of the aforementioned medical devices;
- (iii) packaging in direct contact with a pharmaceutical active ingredient and/or dosage form that is intended for inhalation, injection, intravenous, nasal, ophthalmic (eye), digestive, or topical (skin) administration;
- (iv) tobacco related products and applications, electronic cigarettes and similar devices.
- (v) safety components in automotive applications, for example: air bags, air bag unit housings and covers, seat belt mechanisms, brake systems, pedals and pedal supports, steering systems.

The product(s) may not be used in:

- (i) U.S. FDA Class III Medical Devices; Health Canada Class IV Medical Devices; European Class III Medical Devices;
- (ii) applications involving permanent implantation into the body;
- (iii) life-sustaining medical applications.

All references to U.S. FDA, Health Canada, and European Union regulations include another country's equivalent regulatory classification.

In addition to the above, LyondellBasell may further prohibit or restrict the use of its products in certain applications. For further information, please contact a LyondellBasell representative.

Trademarks

Adflex, Adstif, Adsyl, Akoafloor, Akoalit, Alastian, Alathon, Alkylate, Amazing Chemistry, Aquamarine, Aquathene, Avant, Catalloy, Clyrell, CRP, Crystex, Dexflex, Duopac, Duoprime, Explore & Experiment, Filmex, Flexathene, Fueling the power to win, Glacido, Hifax, Hiflex, Histif, Hostacom, Hostalen, Hyperzone, Ideal, Indure, Integrate, Koattro, LIPP, Lucalen, Luflexen, Lupolen, Luposim, Lupostress, Lupotech, Metocene, Microthene, Moplen, MPDIOL, Nerolex, Nexprene, Petrothene, Plexar, Polymeg, Pristene, Prodflex, Pro-fax, Punctilious, Purell, Refax, SAA100, SAA101, Sequel, Softell, Spherilene, Spheripol, Spherizone, Starflex, Stretchene, Superflex, TBAC, Tebol, T-Hydro, Toppyl, Trans4m, Tufflo, Ultrathene, Vacido and Valtec are trademarks owned and/or used by the LyondellBasell family of companies.

Adsyl, Akoafloor, Akoalit, Alastian, Alathon, Aquamarine, Avant, CRP, Crystex, Dexflex, Duopac, Duoprime, Explore & Experiment, Filmex, Flexathene, Hifax, Hostacom, Hostalen, Ideal, Integrate, Koattro, Lucalen, Lupolen, Metocene, Microthene, Moplen, MPDIOL, Nexprene, Petrothene, Plexar, Polymeg, Pristene, Pro-fax, Punctilious, Purell, Sequel, Softell, Spheripol, Spherizone, Starflex, Tebol, T-Hydro, Toppyl, Tufflo and Ultrathene are registered in the U.S. Patent and Trademark Office.

